

February 20, 2002

## **INSTRUCTION FOR p/n 02-175170 & 02-175180**

Part # 02-175180 has replaced part # 02-175170. This is part of a redesign of the STAPHGUARD door and pressure plate assembly. The new gasket (enclosed) uses a hole pattern which is different than the original gasket. However, the gasket may be used on the older style door by simply drilling the rubber gasket material to fit the original stainless steel liner on the door. The extra holes would be tucked underneath the stainless steel pressure plate and thus should not provide any problem with leaking through the gasket.

This allows us to use one gasket for both old and new style STAPHGUARD door pressure plate assemblies.

Please overlay the stainless steel liner assembly onto the new gasket. Mark, drill or punch the new holes as necessary to allow this gasket to work properly with the existing pressure plate and stainless steel liner.

Best regards,

MILNOR Tech Support

GLL/das  
2/20/02